

FEATURES

- **Flexible design:** Easily adapts to different shapes and surfaces, making installation straightforward.
- **IP54 rating:** Offers protection against dust and splashes, suitable for indoor and semi-outdoor use.
- **Warm white LED colour:** Creates a cosy and welcoming atmosphere, ideal for ambient lighting.
- **60 LEDs per metre:** Ensures consistent and bright illumination across the strip.
- **4.8 W/m power consumption:** Energy-efficient, reducing electricity costs while maintaining brightness.
- **16.6 mm LED pitch:** Provides uniform light distribution without dark spots.
- **24 V DC operation:** Compatible with standard power supplies, ensuring easy integration.

RS PRO Flexible LED Strip Light, Warm White

RS Stock No: 558-397



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible LED strip light offers a versatile lighting solution ideal for various environments. With a warm white LED colour, it provides a comfortable and inviting illumination, perfect for both residential and commercial settings. The strip is designed to be flexible, allowing for easy installation in a variety of configurations.

General Specifications

Colour Temperature	2800-3200 K
Flexible/Rigid	Flexible
LED Colour	Warm White
LED Pitch	16.6 mm
Number of LEDs Per Metre	60
Product Type	LED Strip Light
Typical Luminous Flux (lm/m)	415 lm/m

Protection Category

IP Rating	IP54
-----------	------

Electrical Specifications

Power Per Metre	4.8 W/m
Voltage	24 V dc

Approvals

Standards/Approvals	CE, RoHS
---------------------	----------

Mechanical Specifications

Strip Length	5 m
Strip Width	8 mm

