



Product data sheet

Power tools for trade & industry

Cordless Wood Nailer

GNH 18V-64 MD



Gasless, cordless 15 ga (1.8 mm) nail gun with pneumatic performance and bump fire mode

The most important data

Nail length	32 – 64 mm
Nail diameter	1.8 mm
Triggering system	Full sequential actuation + contact actuation with automatic reversion

Part Number 0 601 482 201

Technical data

Technical data

Collation angle	34 °
Nail diameter	1.8 mm
Nail length	32 – 64 mm
Nail/Staple type	DA finish nail
Triggering system	Full sequential actuation + contact actuation with automatic reversion
Weight excl. battery	3.1 kg
Battery voltage	18.0 V
Magazine capacity	105 Pcs
Packaging dimensions (width x length x height)	360 x 444 x 254 mm
Compatible nails/staples	Bosch nails, Other
BITURBO	No

Noise/vibration information

Total vibration values

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cordless freedom with the power of a pneumatic tool – without compressors, gas cartridges, or cords
- Activate and operate the tool with just one hand thanks to the thumb-actuated power switch
- Gentle on your wrist and lungs thanks to very low recoil and gasless operation

