




ALCOSWITCH

TE Internal #: 9-1437622-6

Aluminum 5056, Straight Knurl with Bar Pointer Knob Design, 6.35 mm [.25 in] Shaft, 19.1 mm [.75 in] Diameter, Black, Line Indicator, Switch Knobs

[View on TE.com >](#)

Switches > Switch Knobs



Primary Product Material: **Aluminum 5056**  
 Knob Design: **Straight Knurl with Bar Pointer**  
 Shaft Size: **6.35 mm [.25 in]**  
 Product Diameter: **19.1 mm [.75 in]**  
 Primary Product Color: **Black**

**Features**

**Configuration Features**

|             |                                 |
|-------------|---------------------------------|
| Spinner     | Without                         |
| Skirt       | Without                         |
| Spin Plate  | Without                         |
| Knob Design | Straight Knurl with Bar Pointer |

**Body Features**

|                          |               |
|--------------------------|---------------|
| Primary Product Material | Aluminum 5056 |
| Primary Product Color    | Black         |

**Dimensions**

|                  |                  |
|------------------|------------------|
| Shaft Size       | 6.35 mm [.25 in] |
| Product Diameter | 19.1 mm [.75 in] |

**Identification Marking**

|                    |      |
|--------------------|------|
| Indicator Style    | Line |
| Indicator Location | Side |

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Not Compliant   |
| EU ELV Directive 2000/53/EC                   | Not Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold  |
| EU REACH Regulation (EC) No. 1907/2006        | <p>Current ECHA Candidate List: JAN 2025 (247)</p> <p>Candidate List Declared Against: JUNE 2024 (241)</p> <p>SVHC &gt; Threshold:</p> <p>Pb (.6% in Component Part)</p> <p><b>Article Safe Usage Statements:</b><br/>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p> |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Not applicable for solder process capability  |


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



## Customers Also Bought



TE Part #42844-1  
RECEPT,PIDG FASTON 14-12 250



TE Part #88048-4  
FFC PIN CONTACT AU




TE Part #206486-2  
CPC RECPT ASSEMBLY SIZE 11-9



TE Part #211401-4  
RECEPT,SZ 13-7,CPC



TE Part #350738-1  
15P UMNL PIN HDR ASSY 94VO




TE Part #1-1437436-0  
CR0002=RLY SKT - 34121-01



TE Part #5-1437567-3  
MPG206R=(MSPG) SW PUSHBUTTON



TE Part #6-1437624-1  
PKG50B1/8=KNOB PLASTIC 1/8 LEX



TE Part #2-1618241-8  
K81B235=RELAY, VACUUM, SPST-NC



TE Part #1-1879499-4  
CRGH2010 5% 3R6 1W

## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_9-1437622-6\\_A\\_c-9-1437622-6-a.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_9-1437622-6\\_A\\_c-9-1437622-6-a.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_9-1437622-6\\_A\\_c-9-1437622-6-a.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.