

115.111.129.98GWAWellenböcke

## Shaft support blocks GWA40-B (Series GWA)

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

D	40 mm
H	86 mm
B	108 mm
L	32 mm
B <sub>1</sub>	56 mm
H <sub>2</sub>	50 mm Tolerance: +/-0,015
H <sub>8</sub>	12 mm
J <sub>B</sub>	86 mm Tolerance: +/-0,2
K <sub>5</sub>	M10
N <sub>1</sub>	11 mm For fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
N <sub>3</sub>	22 mm
W	6 mm
m	0,67 kg Mass of shaft support block

