

PRODUCT-DETAILS

AMD12922-ST

AMD12922-ST Switch 1-gang Intermediate, SP 10AX, Half rocker size - ST



General Information

Extended Product Type	AMD12922-ST
Product ID	2CLA681000N1101
EAN	8427238097206
Catalog Description	AMD12922-ST Switch 1-gang Intermediate, SP 10AX, Half rocker size - ST
Long Description	Rated voltage: 250Vac Rated current: 10AX Half rocker size

Ordering

EAN	8427238097206
Customs Tariff Number	85365080
Minimum Order Quantity	10 piece

Dimensions

Product Net Depth / Length	0.165 m
Product Net Height	0.06 m
Product Net Width	0.1 m
Product Net Weight	0.034 kg

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	8427238097206
Package Level 1 Depth / Length	0.165 m
Package Level 1 Height	0.06 m
Package Level 1 Width	0.1 m
Package Level 1 Gross Weight	0.34 kg

Technical

Ambient Air Temperature	Operation -5 ... +35 °C Storage -5 ... +50 °C
Degree of Protection	IP20
Mounting Type	Flush mounted (plaster)

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK106930A7740
Declaration of Conformity - CE	No declaration needed
Instructions and Manuals	9AKK106930A7740

Classifications

ETIM 7	EC001590 - Switch
ETIM 8	EC001590 - Installation switch
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switch Assortments → Flush Mounted Range BS - Niessen → Design Millenium → Flush Mounted Inserts with Cover Plate → Mechanical Switch / Push Button

Low Voltage Products and Systems → Switch Assortments → Light / LoadControl → Mechanical Switch / Push Button → Mechanical Switch / Push Button - Flush Mounted → Mechanical Switch / Push Button

