

Features

- Male threaded support
- Releasable locking feature
- Secured by M4 nut or into threaded boss
- No installation tools needed

RS PRO PCB Spacers

RS Stock No.: See table



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Male threaded support posts provide secure fixings for printed circuit boards
- Releasable locking retainer holds board firmly but is easily released
- Can be secured using an M4 nut or mounted directly into a threaded boss
- No installation tools required

Material Specifications

Materials	Nylon 6,6
Type	Snap-In Spacer
Colour	Natural
Flammability Rating	UL94-V2
Working Temperature Range	-40°C to +85°C

Part Specifications

Parameters	0304259	0304261	0304262	0304263	0304265	0304266
Body Height	6.4mm	9.5mm	12.7mm	15.9mm	19.1mm	25.4mm
PCB Hole Dia	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm
PCB Thickness	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm
Thread Size	M4	M4	M4	M4	M4	M4
Threaded Stud Lgth	6.4mm	6.4mm	6.4mm	6.4mm	6.4mm	6.4mm

