

FEATURES

- Multiuse epoxy
- Gel time of epoxy is 4-6 minutes
- Double syringe for an effortless mixing ratio
- Operating temperature of up to 60°C
- Resistant to water and a wide range of solvents.
- Rapid cure of 2 hours at room temperature

RS PRO, 24 ml Transparent Dual Cartridge Epoxy Adhesive for Various Materials

RS Stock No.: 132-605



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS Pro range of quick setting epoxy has been formulated to ensure a reliable and solid adhesive bond. This quick set two-part epoxy adhesive comes in two tubes for an easy and clean application. This high strength and high performance adhesive can be used with most materials such as; glass, wood, metals and plastics.

General Specifications

Material Compatibility	Ceramic, Glass, Metal, Plastic, Stone, Wood
Colour	Transparent
Package Type	Dual Cartridge
Package Size	24ml
Special Features	A Rapid Setting Two-Part Epoxy Adhesive
Chemical Composition	Epoxy Resin
Odour	Mercaptan
Physical Form	Solid
Usable Life (At 23°C)	20g 3 -4 minutes sample
Applications	Bonding, Sealing, Coating
Mix Ratio (By Weight)	100:80 25 100:100 25 100:120 24

Mechanical Specifications

Filler Material	Epoxy
Viscosity Description	10Pa.s 7Pa.s
Peel Strength (Aluminium)	T-piece peel strength (DIN 53282), steel plates pickled in HCl (DIN 53281) Cure Time Bond Strength N/mm ² 3 Days @ room temp. 4

Operation Environment Specifications

Maximum Operating temperature	60°C
-------------------------------	------

