



Example image

APPLICATION PURPOSES

- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Silicone-free (LABS-free)
- Pipe end with blue protection plug

TECHNICAL DATA

Product material	CrNiMo steel 1.4401 (EN 10088)
Surface roughness	1 µm
Thermal expansion	0.0165 mm/(m·K)
Thermal conductivity, pipe	15 W/(m·K)
Specific thermal capacity	500 J/(kg·K)

ACCESSORIES

- Geberit Mapress pipe cutter R
- Geberit Mapress pipe deburrer
- Geberit Mapress insertion distance template with marker pen

Art. no.	DN	d, ø mm	di, ø mm	s mm	L m
These articles are suitable for the following system: Geberit Mapress Stainless Steel					
39031	12	15	13	1	3
39032	15	18	16	1	3
39033	20	22	19.6	1.2	3
39034	25	28	25.6	1.2	3

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
39035	32	35	32	1.5	3
39036	40	42	39	1.5	3
39037	50	54	51	1.5	3
39038	65	76.1	72.1	2	3
39039	80	88.9	84.9	2	3
39040	100	108	104	2	3
39002	12	15	13	1	6
39003	15	18	16	1	6
39004	20	22	19.6	1.2	6
39005	25	28	25.6	1.2	6
39006	32	35	32	1.5	6
39007	40	42	39	1.5	6
39008	50	54	51	1.5	6

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
39009	65	76.1	72.1	2	6
39010	80	88.9	84.9	2	6
39011	100	108	104	2	6

These articles are suitable for the following system: **Geberit Mapress Stainless Steel (FKM blue)**

39031	12	15	13	1	3
39032	15	18	16	1	3
39033	20	22	19.6	1.2	3
39034	25	28	25.6	1.2	3
39035	32	35	32	1.5	3
39036	40	42	39	1.5	3
39037	50	54	51	1.5	3
39038	65	76.1	72.1	2	3
39039	80	88.9	84.9	2	3

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
39040	100	108	104	2	3
39002	12	15	13	1	6
39003	15	18	16	1	6
39004	20	22	19.6	1.2	6
39005	25	28	25.6	1.2	6
39006	32	35	32	1.5	6
39007	40	42	39	1.5	6
39008	50	54	51	1.5	6
39009	65	76.1	72.1	2	6
39010	80	88.9	84.9	2	6
39011	100	108	104	2	6
These articles are suitable for the following system: Geberit Mapress Stainless Steel (gas)					
39031	12	15	13	1	3

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
39032	15	18	16	1	3
39033	20	22	19.6	1.2	3
39034	25	28	25.6	1.2	3
39035	32	35	32	1.5	3
39036	40	42	39	1.5	3
39037	50	54	51	1.5	3
39038	65	76.1	72.1	2	3
39039	80	88.9	84.9	2	3
39040	100	108	104	2	3
39002	12	15	13	1	6
39003	15	18	16	1	6
39004	20	22	19.6	1.2	6
39005	25	28	25.6	1.2	6

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
39006	32	35	32	1.5	6
39007	40	42	39	1.5	6
39008	50	54	51	1.5	6
39009	65	76.1	72.1	2	6
39010	80	88.9	84.9	2	6
39011	100	108	104	2	6

These articles are suitable for the following system: **Geberit Mapress Stainless Steel (silicone-free)**

39031	12	15	13	1	3
39032	15	18	16	1	3
39033	20	22	19.6	1.2	3
39034	25	28	25.6	1.2	3
39035	32	35	32	1.5	3
39036	40	42	39	1.5	3

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
39037	50	54	51	1.5	3
39038	65	76.1	72.1	2	3
39039	80	88.9	84.9	2	3
39040	100	108	104	2	3
39002	12	15	13	1	6
39003	15	18	16	1	6
39004	20	22	19.6	1.2	6
39005	25	28	25.6	1.2	6
39006	32	35	32	1.5	6
39007	40	42	39	1.5	6
39008	50	54	51	1.5	6
39009	65	76.1	72.1	2	6
39010	80	88.9	84.9	2	6

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
39011	100	108	104	2	6