

### General

<b>Carton contents</b>	PT-E550WVP labelling machine 24mm strong adhesive black on yellow 8m tape cassette 12mm flexible ID black on white 8m tape Li-ion rechargeable battery AC adaptor Wrist strap Documentation USB-mini cable Software CD Carry case
<b>Language support</b>	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

### Dimensions & Weights

<b>Without carton</b>	126(w) x 250(d) x 94(h) † 1.05 kg
<b>With carton</b>	393(w) x 334(d) x 126(h) † 3.25 kg
<b>Master carton</b>	413(w) x 348(d) x 390(h) † 11.04 kg

### Built In Features

<b>Keyboard</b>	70 Key Rubber QWERTY/QWERTZ/AZERTY
<b>Dedicated number keypad</b>	Yes
<b>Interfaces</b>	USB, Wi-Fi
<b>Operating system support</b>	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.7to 10.9.
<b>Display type</b>	Backlit Graphic Monochrome LCD with label preview capability
<b>Display resolution</b>	16 characters by 3 lines † 128 x 64 dots
<b>Printing speed</b>	Up to 30mm/second
<b>Print resolution</b>	180dpi
<b>Maximum print height</b>	18.0mm
<b>Cutter type</b>	Auto Full & Half (with cut/pause feature) (fluorine-coated to cut strong adhesive tapes)
<b>Label length</b>	15mm minimum † 999mm maximum
<b>Maximum lines per label</b>	7 (for 24mm wide tape)
<b>Tape margins</b>	Auto Cut: On/Off, Half Cut: On/Off, Chain Printing: On/Off, Special Tape: On/Off
<b>Vertical text printing</b>	Yes
<b>Mirror printing</b>	No
<b>Copies</b>	1 to 99
<b>Automatic numbering</b>	Yes (1 – 99, Normal, Simultaneous, Advanced)

### Label Creation

<b>Smart label application keys</b>	General, Faceplate, Cable Wrap, Cable Flag, Heat Shrink Tube, Patch Panel , Punch Down Block
<b>Fonts</b>	14 † Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Calgary, Belgium, Atlanta, Adams, Brunei, Sofia, Germany, Letter Gothic
<b>Font styles</b>	9 (excl. Normal) † Normal, Bold, Outline, Shadow, Solid, Italic, Italic Bold, Italic Outline, Italic Shadow, Italic Solid
<b>Font sizes</b>	6, 9, 12, 18, 24, 36, 42 , 48 point
<b>Symbols</b>	384
<b>Frames</b>	7
<b>Barcodes</b>	9 † CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128), CODE128

### Memory

<b>Max. characters per label</b>	1,500
<b>Label memory locations</b>	99 (or up to 18,297 characters)
<b>Transferred content</b>	6 MB † Label templates: up to 99 Custom symbols: up to 99 Databases: up to 99

### Supplies

<b>Tape type</b>	TZe, HGe, HSe (Heat Shrink Tube)
<b>Tape widths</b>	3.5, 6, 9, 12, 18 & 24mm

### Optional Accessories

<b>Batteries</b>	BA-E001 Li-ion rechargeable battery AA alkaline/rechargeable batteries (LR6/HR6) x 6
<b>AC adaptor</b>	AD-E001