

Product data sheet for uvex u-fit strong N2000



Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG
Elso-Klöver-Str. 6
D-21337 Lüneburg
uvex-safety.de

The uvex u-fit disposable safety glove excels thanks to its impressive mechanical resistance. It is flexible and robust, provides good protection against chemicals and splashes – and is perfect for cleaning work, laboratory work or the food industry.

Features

- Extremely flexible
- Very good tactile feel

Material number	60962
Sizes	L,M,S,XL,XXL
Standard	EN ISO 21420:2020, EN ISO 374-1:2016 + A1:2018, EN ISO 374-4:2019, EN ISO 374-5:2016
Test chemicals	n-Heptane (J), Sodium hydroxide 40% (K), Sulphuric acid 96% (L), Ammonia water 25% (O), Hydrogen peroxide 30% (P), Hydrofluoric acid 40% (S), Formaldehyde 37% (T)
Outer material	No lining
Coating	Nitrile rubber (NBR)
Coating surface area	Fully coated
Coating thickness	0.20 mm
Type	With rolled edge
Colour	Blue
Glove length	28 cm