

AIR HOSE REEL 10 MM



939 C1

PROMO

- Model with automatic hose rewind with holding device
- Shock resistant plastic casing with swivel bracket for attachment to wall
- Conformity to Machine Regulation 2006/42/CE and to the norms ISO EN 12100-1 e ISO EN 12100-2
- Can also be used outdoors
- Glossy polyurethane hose

Hose length (m)	16
Lenght of feeding hose (m)	1,5
Max pressure (bar)	15
Ø internal hose (mm)	10
Output threaded male connector	3/8

Family details

Code	LxPxH mm	Weight kg	Quantity for packaging
U09390004	450x400x230	8,0	1

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000