



Datasheet

ENGLISH

Humidity Control Products

RS Stock number [838-732](#)



Specifications:

Desiccant Content:	30g
Material:	Polycarbonate
Colour:	Black
Operating Temperature:	-40°C to +70°C, reactivation +120°C
Environment Protection:	Resistant to alcohols, ethers, hydrocarbons, weak acids and bases
Typical Application Volume	
IP67 Enclosure:	30 Litres/ approx. 6-9 months
IP55 Enclosure:	30 Litres/ approx. 3-6months
Reactivation:	4 hours in a ventilated oven @ 120 °C
Maximum Pressure:	1 bar gauge
Maximum Vacuum:	500 Torr (-5 psi)
Maximum Leak Rate:	1.3 10 ⁻² cc/sec
Humidity indicating Level:	30% RH @ 20 °C and 50% RH @ 20 °C
Tightening Torque:	2Nm

Drawing(mm):

