

Features

- Dielectric strength is 13 kV
- Tensile strength at break is >6.5 MPa
- Tear strength is >10 Kn/m
- Ultimate elongation of >500%
- Flame retardant
- Operating temperature ranging between -30°C and 90°C

RS Stock No.: RS PRO HHP



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO HHP expandable cable sleeve provides reliable protection in a compact 3 mm diameter and 25m length. Manufactured from highly elastic polychloroprene rubber, it offers strong mechanical performance along with excellent resistance to ozone, oils, moisture, and aromatic fuels.

General Specifications

Part Number	Internal Diameter (mm)	Wall Thickness (mm)	Cut Length (mm)
0848960	1.75	0.5	20
0848984	2.00	0.5	20
0848971	2.50	0.6	20
0848949	3.00	0.6	25
0848970	3.00	0.6	25
0848982	3.00	0.6	20
0848966	3.00	0.6	25
0848985	3.00	0.6	25
0848977	4.00	1.2	30
0848988	4.00	1.2	30
0848983	5.00	0.7	25
0848987	5.00	0.7	25
0848955	5.00	0.7	25
0848986	7.50	0.8	25
0848958	7.50	0.8	30
0848963	10.00	0.9	35
0848957	12.00	1.2	50