



ENGLISH

Datasheet

## RS Pro Non-Fused Terminal Block, 12 Way/Pole, Screw Down Terminals, 10 mm<sup>2</sup> Through Hole, Nylon, 400 V

RS Stock No: **492-8722**



### Product Details

RS Pro non-fused terminal block in natural colour, has 12-way terminal blocks. This through hole block with 10-mm<sup>2</sup> wire, features screw down termination. The terminal block made of nylon, has 400 V voltage rating.

### Features and Benefits

- Brass contact material
- Nickel contact plating
- Current rating of 57 A
- 15 mm pitch

**Specifications:**

Contact Material	Brass
Contact Plating	Nickel
Current Rating	57 A
Material	Nylon
Maximum Operating Temperature	+125°C
Mounting Type	Through Hole
Number of Ways	12
Pitch	15 mm
Termination Method	Screw Down
Voltage Rating	400 V
Wire Size	10 mm <sup>2</sup>
Colour	Natural
Screw Size	M3 x 6
Standards Met	RoHS, CE, UL 94V-2, IEC 695-2-1, 2