

FEATURES

- IP66 and 67 Rated
- Voltage ratings of 415V
- All models offered in the range are highly reliable and excellent quality
- Straight body orientation
- Strong twist lock mechanism

RS PRO IP66, IP67 Red Cable Mount 6P+E Industrial Power Plug, Rated At 16.0A, 415.0 V

RS Stock No.: 893-7969



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, comes a range of high-quality cable mounted power connectors. Manufactured to industry standards these red connectors are easy to assemble and is a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

General Specifications

Commercial Series	Optima Seven
Syntetical Description	PLUG
Pole Format	6P+E
Hour Position	6h
Gender	Male
Body Orientation	Straight
Material	Engineering Plastic
Colour	Red
Locking Mechanism	Strong twist
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Type of Current	AC
Current Rating	16A
Voltage Rating	415.0 V
Working Frequency	50Hz; 60Hz
Plug/Socket	Plug
Termination Method	Screw

Mechanical Specifications

Mounting Type	Cable Mount
----------------------	-------------

Protection Category

IP Rating	IP66, IP67
-----------	------------

Approvals

Compliance/Certifications	EN60309-1, 1/A1, 1/A2, CE
---------------------------	---------------------------

