



140
kg



● Sternal | ● Dorsal | ● Lateral | ● Ventral



HS CODE
63079098
CARTON SIZE / PCS.
60 X 40 X 24 cm / 5
AET (EU) N°2777/10346-03/E03-02
Satra Technology Europe Ltd., N° 2777, Bracetown Business Park, Clonee, Dublin, D15YN2P, Ireland
MODULE D FI14/14003.01
SGS Fimko Oy, N°0598 Takomotie 8, 00380 HELSINKI, Finland

REF.	FA 10 206 00A FA 10 206 01A FA 10 206 02A
SIZES  KG	S-M M-L L-XXL MAX. 140 KG (PPE-R 11.132)
CE	EN 361:2002, EN 358:2018, EN 813:2008
Attachment	Dorsal (A), Sternal (A), Lateral, Ventral
 / 	4 / 2
MAT.  / 	
MAT.  45 mm	Polyester
 /  / 	3 / 3 / 2
	2.43 KG 2.46 KG 2.51 KG

SIZES  KG	 / 	MAT.  / 
Taille Poids maxi utilisateur Size Max. user weight Tamaño Peso máximo del usuario Dimensione Größe Höchstgewicht des Benutzers	Nombre de boucles de réglage / boucles automatiques Number of adjustment buckles / automatic buckles Cantidad de hebillas de ajuste / hebillas automáticas Numero di fibbie di regolazione / fibbie autobloccanti Anzahl der Einstellschnallen / Schnellverschluss-Schnallen	Matière des / boucles Material of rings / buckles Material de anillas en D / hebillas Materia del D / Fibbie Material D-Ringe/Schnallen
	 /  / 	
	Nombre de dés porte-outils / poignées porte-matériel / triangles porte-accessoires Number of tool-holding D-rings/equipment-holding handles/accessory-holding triangles Cantidad de anillas en D portaherramientas / asas portamateriales / triángulos portaccesorios Numero di portautensili / maniglie portamateriale / triangoli portaccessori Anzahl der Werkzeug-D-Ringe / Werkzeug-Halteringe / Zubehör-Triangel	