

ML3390eco/ML3391eco Specifications

OKI
PRINTING SOLUTIONS



Fast, reliable and eco-friendly 24-pin printers that deliver real value for money

Reliable, high quality printing that's energy efficient

The ML3390eco and 136 column ML3391eco dot matrix printers are suited to a wide range of high speed data listing and multi-part forms applications, where presentation and print quality are essential.

Designed to work in the most demanding of environments these tough desktop printers have provided over 10 years of dependable service to business. Now enhanced with the latest power management technology power consumption is reduced to just 1.5W in "Sleep mode" to deliver significant energy savings over the products long life.

Versatile paper handling for a wide range of applications

The ML3390/1eco printers can handle cut sheets, continuous feed paper and multi-part forms. Perfect for printing receipts, invoices, picking lists, reports and spread sheets working across a wide range of retail and production environments. Its 24-pin print head can produce up to 5 high quality documents simultaneously for high efficiency working.

Top, bottom and rear paper input paths and a built-in rear push tractor feed unit provide flexibility.

Optional bottom push and top pull tractor units are available to allow the loading of two different media types simultaneously or the feeding of heavier papers and labels. A Roll Paper Stand option is available for the ML3390eco for economical printing of passenger lists, call logs, data logs etc.

Environmentally friendly

The ML3390/1eco printers have been developed to be eco-friendly. OKI's SoC (System on Chip) technology reduces power consumption to an impressively low 1.5W in "Sleep mode" keeping your running costs and energy consumption to a minimum, as well as reducing your carbon footprint.

OKI's commitment to customers

The OKI brand is one of proven reliability and value. With almost half a century of experience in the impact printer industry, you are guaranteed a best-in-class performance and great value for money products. And, for total peace of mind, just register your printer and take advantage of our extended three year on-site warranty at no extra cost.

Highlights:

- Up to 390 characters per second (cps) print speed
- 80 and 136 column versions available
- IBM and Epson emulations
- Comprehensive range of scalable fonts and barcode support
- Eco-friendly technology, sleep mode consumes just 1.5W
- 24-pin print head delivers sharp, detailed text
- Multi-part paper-handling (original + 4 copies)
- Easy change 2 million character cartridge ribbon
- Low-tear and auto-park help eliminate wastage
- USB and Parallel interfaces with RS232 and Network options
- Manufactured at a CarbonZero facility
- Three-year warranty as standard (product registration required)

Variants available:

ML3390eco
Narrow carriage

ML3391eco
Wide carriage



ML3390eco and ML3391eco - Dot Matrix Printers

PRINTER		GENERAL FEATURES	
Number of pins	24	Input buffer	128Kbytes
Columns	ML3390eco: 80 (10cpi); 160 (maximum in compression mode) ML3391eco: 136 (10cpi); 272 (maximum in compression mode)	Power supply	Single phase 220 to 240VAC, +/- 10%, frequency 50/60Hz
Character pitch	10/12/15/17.1/20 pitch and proportional	Power consumption	ISO/IEC 10561 Letter, Draft, Range1: 30.4W; Sleep mode: <1.5W (with no optional attachments)
Graphics resolution	Up to 360 x 360dpi	Noise level	Normal: 57dB(A); Quiet: 52dB(A)
Print speed	Fastest Print Speed: 390cps; Utility: 312cps (12cpi), 260cps (10cpi); Letter Quality: 104cps (12cpi), 87cps (10cpi)	Dimensions (HxWxD)	ML3390eco: 116 x 398 x 345mm ML3391eco: 116 x 552 x 345mm
INTERFACE AND EMULATIONS		Weight	ML3390eco: 5.8kg approx; ML3391eco: 7.6kg approx
Interfaces	Centronics IEEE 1284 parallel interface, USB 2.0	Print head life	200 million characters
Optional interfaces	Ethernet 10/100, Serial RS232C	Reliability	MTBF: 10,000 hours
Emulations	Epson LQ ESC/P2, IBM ProPrinter, IBM AGM	Warranty	3 years extended warranty upon registration within 30 days of purchase
Typeface & font	Utility, Courier (scalable), Roman (scalable), Swiss (scalable), Swiss Bold, Prestige, Gothic, Orator, OCR-A, OCR-B	Product order numbers	ML3390eco: 01308402; ML3391eco: 01308502
Typestyle	Emphasised, Enhanced, Double Width, Double Height, Italics, Outline, Shadow, Bold, Superscript, Subscript, Underline	ACCESSORIES (ORDER NUMBERS)	
Barcodes	UPC-A, UPC-E, EAN8, EAN13, Code39, Interleaved 2of5, Code128 (A/B/C), POSTNET	Single Bin Cut Sheet Feeder	ML3390eco: 44497402; ML3391eco: 44497502
Printer driver ¹	Windows 2000 / XP (32-bit & 64-bit) / Vista (32-bit & 64-bit) / 7 (32-bit & 64-bit) / Server 2003 (32-bit & 64-bit) / Server 2008 (32-bit & 64-bit) / Server 2003	Push Tractor (bottom feed)	ML3390eco: 09002366; ML3391eco: 09002370
PAPER HANDLING		Pull Tractor (bottom/rear feeds)	ML3390eco: 09002365; ML3391eco: 09002369
Paper	Cut Sheet (single sheet), Continuous Paper (single-part, multi-part), Roll paper (ML3390eco only), Envelope, Card, Label (cut sheet and fan fold)	Roll Paper Stand	09002332 (ML3390eco only)
Continuous paper (width)	ML3390eco: 76.2 - 254mm; ML3391eco: 76.2 - 406.4mm	Serial RS232C	44455102
Continuous envelopes	ML3390eco: 165 x 92mm ML3391eco: 241 x 105mm (Bottom feed only)	Network Card	44455302
First printable line (from top of page)	Continuous (multi-parts): 0.5mm Cut sheet (single sheet): 0.5mm	CONSUMABLES (ORDER NUMBER)	
No. of multi-part forms	Up to 5 (one original + 4 copies)	Ribbon (2 million characters)	09002309
Multi-part paper thickness	Bottom push feed: 0.44mm; rear push feed & top/rear push-pull feed: 0.36mm; Bottom pull feed: 0.44mm		
Paper feeding	Manual insertion: Top in, top out; Push Tractor: rear in, top out; Optional Push/Pull tractor: rear or bottom in, top out		
Optional paper feeding	Single Bin Cut Sheet Feeder, Bottom Push Tractor (bottom feed), Top mounted Pull Tractor (bottom/rear feed), Roll Paper Stand (ML3390eco only)		

¹Check local OKI Printing Solutions website for latest driver releases and OS compatibility

Consumables Information: Only use genuine OKI Printing Solutions Original consumables to ensure the best quality and performance from your hardware. Non OKI Printing Solutions Original products may damage your printer's performance and invalidate your warranty.



Simply Unique - 3 Year Warranty

Our devices are manufactured to the highest standards of quality and technology, which has been confirmed by independent tests. We are so convinced of the high quality of our products that we are offering you an extension of the standard warranty period to 3 years – for free! Simply register your product within 30 days of purchase to be eligible for our unique all inclusive offer. Fully covered by OKI! For further information please visit: www.okiprintingsolutions.co.uk/warranty. Without registration, the standard pan-European 1 year warranty applies.

WARNING! This product complies with EN55022 Class B. However when fitted with the optional network interface card or optional cut sheet feeder, compliance to EN55022 is Class A. In a domestic environment this configuration may cause radio interference, in which case the user may be required to take adequate control measures.



© 2011 Oki Europe Ltd. Oki Printing Solutions is the trading name of Oki Europe Ltd. Version 1.0 02/2011. Specification subject to change without notice. All trademarks acknowledged.

OKI SYSTEMS (UK) LTD.

550 Dundee Road, Slough
Berkshire, SL1 4LE
United Kingdom
T +44(0) 1753 819819
F +44(0) 1753 819899

www.okiprintingsolutions.co.uk

OKI
PRINTING SOLUTIONS