

# Specifications

## Eaton 5P850IRNG2BS

Eaton 5P Gen2 UPS, 850 VA, 680 W, Input: C14, Outputs: (4) C13, Rack, 1U, Network card, BS Input cord



### General specifications

PRODUCT NAME	Eaton 5P Gen2 UPS
CATALOG NUMBER	5P850IRNG2BS
EAN	3553340710490
PRODUCT LENGTH/DEPTH	509 mm
PRODUCT HEIGHT	43.2 mm
PRODUCT WIDTH	438 mm
PRODUCT WEIGHT	14.043 kg
WARRANTY	3 year on electronics, 2 year on battery
COMPLIANCES	LVD Directive (CB) EMC Directive RoHS Directive WEEE Directive Packaging Directive Batteries Directive
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 IEC/EN 62040-3 UL 1778 CSA-C22.2 CE UKCA Cm Ukr KCC cTUVus BIS

Battery	
BATTERY TYPE	Lead-acid maintenance-free (replaceable)
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY REPLACEMENT	User replaceable
BATTERY QUANTITY	4
BATTERY MANAGEMENT	ABM or constant voltage charging method (user selectable), automatic battery test, deep discharge protection
BATTERY RATING	6 V / 7 Ah
EXTENDED BATTERY CAPABILITY	No

Electrical input	
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50-60 Hz
INPUT VOLTAGE RANGE	160-294 V (adjustable to 150 V-294 V)
INPUT FREQUENCY RANGE	47-70 Hz (50 Hz system), 56.5-70 Hz (60 Hz system), 40 Hz in low sensitivity mode

Environmental	
ALTITUDE	3000 m
NOISE LEVEL	<35 dB at 1 meter
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
RELATIVE HUMIDITY	0-90% non-condensing

Electrical output	
RECEPTACLE	(4) C13
VOLTAGE	230V
WATTAGE	680
OUTPUT POWER FACTOR	0,8
OUTPUT VOLTAGE RANGE	230 V (+6%/-10%)
OUTPUT WAVEFORM	Sine wave
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
TOPOLOGY	Line-interactive
VA RATING	850 VA

Communications	
INCLUDES NETWORK CARD	Yes
COMMUNICATION	<ul style="list-style-type: none"><li>• USB port (HID compliant)</li><li>• Serial port (RS232)</li><li>• Mini-terminal block for remote On/Off and Remote Power Off</li><li>• Dry contacts (2 outputs, optocoupler, RJ)</li></ul>
ETHERNET INTERFACE	Yes
USER INTERFACE	Multilingual graphical LCD display
POTENTIAL FREE SWITCH CONTACT	Yes
EXPANSION SLOTS	One slot for optional communication card
SOFTWARE COMPATIBILITY	Eaton Brightlayer Software suite
TYPE OF INTERFACE	Other

Additional specifications	
CONSTRUCTION TYPE	482.6 mm (19 inch) device
ENCLOSURE	Black/silver
PACKAGE CONTENTS	<ul style="list-style-type: none"><li>• Rack-mounting kit</li><li>• Cable locking system</li><li>• USB cable</li><li>• (2) IEC-IEC cables</li><li>• Quickstart guide</li><li>• Safety instructions</li><li>• Network card</li><li>• BS Input cord</li></ul>

<b>PHASE (OUTPUT)</b>	1
<b>AUTO SHUTDOWN FUNCTION</b>	Yes
<b>COLOR</b>	Black/silver
<b>EFFICIENCY</b>	98
<b>RACK MOUNTING KIT</b>	Yes
<b>PHASE (INPUT)</b>	1

## Resources

<b>BROCHURES</b>	<a href="#">Eaton 5P Gen2 UPS datasheet</a>
<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">EU Declaration of conformity Eaton 5P Gen2 UPS</a>
<b>MANUALS AND USER GUIDES</b>	<a href="#">Eaton 5P Gen2 Quick Start Guide</a> <a href="#">Eaton 5P Gen2 Rack - Advanced user guide</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

