



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 7 Watt, 200-2M Ohm



Resistance Value: 12K Ω

Resistor Type: **Power Resistor**

Element Type: **Metal Film**

Power Rating: 2 W

Resistance Class: 1k Ω – 1M Ω

[All SMD Power Resistor: 7 Watt, 200-2M Ohm \(316\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	300 V
Resistance Value	12K Ω
Power Rating	2 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	3.55 mm[.14 in]
Product Length	6.7 mm[.264 in]



Product Width	4 mm[.157 in]
---------------	---------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Industry Standards

UL Flammability Rating	UL 94V-0
ESD HBM Classification	2
Moisture Sensitivity Level	1

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMF212KJT

12K ohm, Surface Mount Power Resistor, Metal Film, 2 W, 5 %, ±100 ppm/°C, Solder, 2 Terminations, 3.55 mm [.14 in] Height, CGS SM



TE Part # 3-2176619-9
SMQF2W 12K 5%

TE Part # 1879233-9
SMW5 R22 5%

TE Part # CAT-C339-SM1
SMD Power Resistor: 7 Watt, 200-2M Ohm

Also in the Series | CGS SM

Expanded Beam Fiber Optics(6)

LC Connectors(1)

RJ14 Connectors(1)

RJ22 Connectors(1)

RJ25 Connectors(1)

RJ45 Connectors(3)

SC Connectors(2)

Surface Mount Resistors(549)

Customers Also Bought

TE Part #8-1625867-4
RP 1J 0.166W 46R4 0.1% 25PPM 1K RL

TE Part #1445336-3
LOOSE PC CONTACT 30 AU PLATED

TE Part #2176058-6
RLP73V 3A R016 5% 2K RL

TE Part #CAT-104MTA-PVUMH
PCB Header: Polyester, Vertical, 2.54 mm

TE Part #176153-3
EIS POST HDR ASSY H 3P GOLD

TE Part #3-2176368-7
RQ 0603 118K 0.1% 10PPM 1K RL

TE Part #3-2176087-3
RP 1J 0.166W 147R 0.1% 25PPM 1K RL

TE Part #643067-3
03P MTA156 MOLDED COVER

SMF212KJT

12K ohm, Surface Mount Power Resistor, Metal Film, 2 W, 5 %, ±100 ppm/°C, Solder, 2 Terminations, 3.55 mm [.14 in] Height, CGS SM



Documents

Product Drawings

SMF2 12K 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1879011-3_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1879011-3_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1879011-3_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

SMD Moulded Power Resistor - Type SM Series - Tyco Electronics Passives

English