



**Part Number :** [439151213](#)  
**Product Description :** 10.00mm Pitch Mini-Fit Sr.  
Header, Dual Row, Vertical, 3.18mm PCB Thickness,  
0.76µm Gold (Au) Selective Plating, 10 Circuits  
**Series Number :** 43915  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles



## Documents & Resources

### Drawings

[439151213 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Compliant with Exemption 33; 44;<br>34                                                                       |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Not Low-Halogen per IEC<br>61249-2-21                                                                        |
| REACH SVHC         | Not Contained per D(2025)4165-DC<br>(25 June 2025)                                                           |
| EU RoHS            | Compliant per EU 2015/863                                                                                    |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                                                              |
|----------------|------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                       |
| Category       | PCB Headers and Receptacles                                                                                                  |
| Series         | 43915                                                                                                                        |
| Description    | 10.00mm Pitch Mini-Fit Sr. Header, Dual Row, Vertical, 3.18mm PCB Thickness, 0.76µm Gold (Au) Selective Plating, 10 Circuits |
| Application    | Power, Wire-to-Board                                                                                                         |
| Component Type | PCB Header                                                                                                                   |
| Product Name   | Mini-Fit Sr.                                                                                                                 |
| UPC            | 800756521367                                                                                                                 |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 50.0A |
| Voltage - Maximum             | 600V  |

### Physical

|                    |       |
|--------------------|-------|
| Breakaway          | No    |
| Circuits (Loaded)  | 10    |
| Circuits (maximum) | 10    |
| Color - Resin      | Black |

|                                |                                |
|--------------------------------|--------------------------------|
| Durability (mating cycles max) | 100                            |
| First Mate / Last Break        | No                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | Yes                            |
| Material - Metal               | Brass                          |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 22.534/g                       |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| Packaging Type                 | Tray                           |
| PCB Locator                    | Yes                            |
| PCB Retention                  | Yes                            |
| PCB Thickness - Recommended    | 3.18mm                         |
| PC Tail Length                 | 5.10mm                         |
| Pitch - Mating Interface       | 10.00mm                        |
| Pitch - Termination Interface  | 10.00mm                        |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 2.540µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| Shrouded                       | Fully                          |
| Stackable                      | No                             |
| Temperature Range - Operating  | -40° to +105°C                 |
| Termination Interface Style    | Through Hole                   |

### Solder Process Data

|                              |          |
|------------------------------|----------|
| Max-Duration                 | 30       |
| Lead-Free Process Capability | SMC&WAVE |
| Max-Cycle                    | 3        |
| Max-Temp                     | 235      |

---

## Mates With / Use With

### Mates with Part(s)

| Description                               | Part Number  |
|-------------------------------------------|--------------|
| Mini-Fit Sr. Dual Row Receptacle Housings | <u>43914</u> |