Endress+Hauser Pressure sensor PMD55-GA22AD67HGBHAJA2A

Differential pressure transmitter with metal sensor for continuous measurement of pressure differences in liquids, vapors, gases and dusts. Used in environmental or process industries.



Picture for reference only. Product appearance may vary based on configuration

Configuration of PMD55-GA22AD67HGBHAJA2A:

Approval:	GA	EAC Ex ia IIC T6 Ga/Gb
Output:	2	4-20mA HART
Display, Operation:	2	W/o LCD, push button on electronics
Housing:	A	F30 Alu
Electrical Connection:	D	Thread NPT1/2, IP66/67 NEMA4X/6P
Nominal Pressure PN:	6	70bar/7MPa/1015psi
Sensor Nominal Value:	7H	3bar/300kPa/45psi
Reference Accuracy:	G	Standard
Calibration; Unit:	B	Nominal value; mbar/bar
Process Connection:	HAJ	NPT1/4-18 IEC61518 UNF7/16-20, 316L, V1 Installation impulse line vertical Alignment 90deg
Membrane Material:	A	316L
Fill Fluid:	2	Inert oil
Seal:	A	FKM Viton

Alternative part number: PMD55-4WU31/0