

cylindrical fuse holder 10 x 38 mm, 1-pole In: 32 A, Un AC: 690 V LED signal detector

Model	
product brand name	SENTRON
product designation	Cylindrical fuse holder
design of the product	LED signal detector
General technical data	
number of poles	1
size of fuse link	10 x 38 mm
Supply voltage	
operating voltage	
• at AC rated value	690 V
protection class IP	IP20
Mechanical Design	
height	81 mm
width	18 mm
depth	64 mm
Net Weight	60 g
Certificates	
reference code according to IEC 81346-2	F
Approvals Certificates	
Environment	General Product Approval

[Environmental Conformations](#)



Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012 Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7014-2 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3NW7014-2 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7014-2 CAX-Online-Generator https://www.siemens.com/cax Tender specifications https://www.siemens.com/specifications Characteristic curves <a href='https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>'>https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>

last modified:

12/11/2025

