

Product details - BROTHER LC-3219XLM Ink Magenta

OEM Item Nr.:	LC3219XLM	
Manufacturer:	BROTHER	
EAN:	4977766762205	
Manufacturer's warranty :	24 Months Warranty	
ArticleGroup:	Print, Scan & Supplies - Supplies - Ink - Inks & Ink Printheads	

Description

BROTHER LC-3219XLM Ink Magenta 1500 pages

Key selling points

- Great value for money
- Guaranteed quality printed documents, every time
- No streaks as the ink viscosity is perfectly measured to suit your printer
- Superior print definition as your ink will safeguard your printer's print head
- Vacuum packed cartridges ensure no air bubbles, no leakages and no ink blotting
- Perfectly balanced inks ensure a longer life for your printer

Technical details

General	
Dimensions (WxDxH) / Weight	8.455 cm x 1.48 cm x 7.07 cm / 52 g
Shipping Width	8 cm
Shipping Depth	12.5 cm
Shipping Height	2 cm
Shipping Weight	61 g
Consumable	
Consumable Type	Ink cartridge
Printing Technology	Ink-jet
Colour	Magenta
Included Qty	1-pack
Cartridge Yield	XL
Yield	Up to 1500 pages ISO/IEC 24711
Miscellaneous	
Packaging Type	Blister
Compatibility Information	
Compatible with	Brother MFC-J5330DW, MFC-J5335DW, MFC-J5730DW, MFC-J5930DW, MFC-J6530DW, MFC-J6935DW Brother Business Smart Pro MFC-J6930DW Brother INKvestment Business Smart Plus MFC-J5930DW Brother INKvestment Business Smart Pro MFC-J6935DW