

# Product data sheet

Specifications

## Exiway - false ceiling kit

OVA59823



### Main

|                                    |                    |
|------------------------------------|--------------------|
| Range                              | Exiway             |
| Product or component type          | Flush mounting kit |
| Accessory / separate part category | Mounting accessory |
| Colour                             | Grey               |

### Complementary

|                       |                                                                                                     |
|-----------------------|-----------------------------------------------------------------------------------------------------|
| Range compatibility   | Exiway Exiway Smartled emergency light fitting                                                      |
| Product compatibility | Exiway Smart<br>Exiway Smartled                                                                     |
| Kit composition       | 1 false ceiling kit<br>2 screw diameter: 4 mm x 70 mm<br>2 washer<br>2 screw diameter: 4 mm x 55 mm |
| Material              | Steel                                                                                               |
| Width                 | 210 mm                                                                                              |
| Height                | 170 mm                                                                                              |
| Depth                 | 42 mm                                                                                               |
| Cut-out dimensions    | 225 x 105 mm (Exiway Smart)<br>278 x 105 mm (Exiway Smartled)                                       |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 4.0 cm   |
| Package 1 Width              | 17.2 cm  |
| Package 1 Length             | 21.0 cm  |
| Package 1 Weight             | 275.0 g  |
| Unit Type of Package 2       | S03      |
| Number of Units in Package 2 | 25       |
| Package 2 Height             | 30 cm    |
| Package 2 Width              | 30 cm    |
| Package 2 Length             | 40 cm    |
| Package 2 Weight             | 7.303 kg |

### Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications





## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

| Materials and Substances               |                           |
|----------------------------------------|---------------------------|
| Packaging made with recycled cardboard | No                        |
| Packaging without single use plastic   | No                        |
| EU RoHS Directive                      | <a href="#">Compliant</a> |

### Use Longer

| Lifetime extension |    |
|--------------------|----|
| Repair             | No |

### Use Again

| Repack and remanufacture |                                                                                                                             |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Take-back                | No                                                                                                                          |
| WEEE Label               | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Image of product / Alternate images

Alternative

---







