

Eaton 250MJ30-7

Catalog Number: 250MJ30-7

Eaton Bussmann series low voltage british standard fuse, 250A, AC 415 V, V88/J, 38 x 110 mm, gU, 82mm fixing centres, type 7

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage british standard fuse	250MJ30-7
	EAN
	5027590469449
Product Length/Depth	Product Height
110 mm	38 mm
Product Width	Product Weight
38 mm	217.6 g
Compliances	Certifications
CE Marked	BS
RoHS Compliant	IEC 60269
	EAC



Electrical data

Amperage Rating

250 A

Voltage rating

415 V

Voltage type

AC

Breaking capacity

80 kA

Class

Other

Product specifications

Application

feeder pillars

Fuse type

MJ30

Fitted with:

Slotted tags

Connection

Bolt-on

Resources

Catalogs

[CA134002EN](#)

Declarations of conformity

[CE Feeder pillar fuse-links](#)

[UKCA Feeder pillar fuse-links](#)

Multimedia

[Eaton Bussmann - Red Spot fuse links](#)

Technical data sheets

[4178A MJ30 and 82AL fuses](#)

Technical service bulletins

[Datasheet - 250MJ30-7](#)