

Product data sheet

Specifications



Repacked, auxiliary contact, Acti9 A9A, iOF/SD+OF, 2 C/O, 100mA to 6A, 24VAC to 415VAC, 24VDC to 130VDC, top and bottom connection

A9A26909W



This repacked option saves 0.29 over the standard condition

Main

range of product	Acti9
Product or component type	Double OC or fault contact
Device short name	iOF/SD+OF
Signal contacts composition	2 C/O
[In] rated current	0.1...6 A at 24...240 V, AC 50/60 Hz 0.1...3 A at 415 V, AC 50/60 Hz 0.1...6 A at 24 V, DC 0.1...2 A at 48 V, DC 0.1...1.5 A at 60 V, DC 0.1...1 A at 130 V, DC
9 mm pitches	1
Standards	EN/IEC 60947-5-1 GB/T 14048.5
Product certifications	CE UKCA
Quality labels	EAC CCC CMIM

Complementary

Range compatibility	Acti9 iC60 Acti9 iLD Acti9 ARA Acti9 RCA Acti9 iDPN Vigi Acti9 iC40 Acti9 iSW-NA Acti9 iCVm40 Acti9 iCVr40 Acti9 iDDm40
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Local signalling	Mechanical indicator
Mounting mode	Clip-on
Mounting location	Left side of circuit-breaker
Mounting support	DIN rail
Comb busbar and distribution block compatibility	NO
Height	90 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	9 mm
Depth	73 mm
Product weight	43 g
Colour	White
Connections - terminals	Screw clamp terminal (top and bottom): 1 cable(s) 0.5...2.5 mm² - flexible Screw clamp terminal (top and bottom): 1 cable(s) 1...4 mm² - rigid Screw clamp terminal (top and bottom): 2 cable(s) 2.5 mm² - rigid Screw clamp terminal (top and bottom): 2 cable(s) 1.5 mm² - flexible with ferrule
Wire stripping length	10 mm
Tightening torque	1 N.m top and bottom

Environment

IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.300 cm
Package 1 Width	7.400 cm
Package 1 Length	9.000 cm
Package 1 Weight	46.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.292 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.3 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

9da5f8d9-d60f-424a-bb30-a856a097686c

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins