



TB-04 0560

E1441282

TERMINAL BLOCK, SCREW MOUNT, WITH LEVER, 4-POLE 0.5-4.0mm2(6mm2 Solid), AWG 28-10



Product Properties:

Number of poles	4 .
Rated voltage	600 V
Explosion-tested version 'Ex e'	No
Rated current In	40 A
Type of electrical connection 1	Plug-in connection
Type of electrical connection 2	Plug-in connection
Number of clamp positions per pole	2 .
Mounting method	Surface mounted
Material insulation body	Thermoplastic
Closing plate required	No
Operating temperature	-40-105 °C
Transparent	No
Colour	Green
Halogen free	Yes
Inflammability class of insulation material according to with UL94	V2

Dimensions:

MOQ	25 .
Unit	pcs
Rated voltage	600 V
Drill hole distance centrically	34.5 mm

Connectable conductor cross section fine-strand without cable end sleeve	0.5-4 mm²
Connectable conductor cross section fine-strand with cable end sleeve	0.5-4 mm²
Connectable conductor cross section solid-core	0.5-6 mm²
Connectable conductor cross section multi-wired	0.5-4 mm²
Rated current In	40 A
Width/grid dimension	40.6 mm
Height at lowest possible mounting height	13.3 mm
Length	36 mm

Approvals:

Approved according to CE	Yes
Approved according to UKCA	Ja
Inflammability class of insulation material according to with UL94	V2

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
PFAS	No PFAS
POPs	No POPs
REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC001284 - Single- and multi-pole terminal strip
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Terminal Block - Push-in
Search Description	SKH2023ERIK1 ENR2023V
Alternative SKU	TB-040560
E-no	E1441282

Logistic information:

Barcode	733117641162
Country of origin	CN
E-no	E1441282
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	25 .
Stock code	TB-04 0560

Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.