

Datasheet

Stock No: 811-4352

RS Pro 3 Core Unscreened Grey 2183Y Power Cable



STANDART	:	TS 9760 HD 21.5 S3
CONDUCTOR	:	Class 5 accoding to IEC 60228
INSULATION	:	PVC
INSULATION COLOR	:	HD 308
SHEATH	:	PVC
OPERATING TEMPERATURE	:	-50 70 °C
NOMINAL VOLTAGE	:	300/300 V
TEST VOLTAGE	:	2 kV

To whom it may concern;

This is to certify that the following technical values are true and comply with the HAR standards

DIAMETERS

No. of Cores and mm ² per conductor	Cu Ø Mm	Insulation thickness		Outer diameter in Mm (0,1mm)	Max. resistance at 20°C (Ω/km)
		Minimum mm	Nominal mm		
2x0,50	15x0,20±0,004	0,35	0,50	5,10	39,00
2x0,75	22x0,20±0,004	0,35	0,50	5,40	26,00