

• Home> 5219324F

Part Number: **5219324F General Description**

Series 521

Configuration 3 mm Lens

Description Discrete LED Lamp

Package Options Bulk Packaging

Sizes 3mm

Lamp Type Single Color

Lens Color Diffused

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA 7mA

Reverse Current 10 @ Vr = 5V

Forward Current Pulsed 500mA

Solder Temperature 260° for 5 sec

Operating Temperature -55~+100

Storage Temperature $-55 \sim +100$

Operating Characteristics

Color Red

LED Type Standard Efficiency

Luminous Intensity Min1Luminous Intensity Typical1.6Test Current mA2mAPower Dissipation Max20mW

Site Map Contact Us Dialight BLP Ltd Privacy Policy Careers





This is a RoHS Compliant Product To learn more click here

Copyright© 2009, Dialight. All Rights Reserved.

050000000000