

## har-SAB M12/8/5p PAC 2m PVC w/o LED



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 09 07 001 2225 300                                                                  |
| Specification      | har-SAB M12/8/5p PAC 2m PVC w/o LED                                                 |
| HARTING eCatalogue | <a href="https://harting.com/09070012225300">https://harting.com/09070012225300</a> |

### Identification

|               |                            |
|---------------|----------------------------|
| Series        | Circular connectors M12    |
| Element       | Distribution boxes         |
| Specification | Pre-assembled master cable |

### Version

|                       |                        |
|-----------------------|------------------------|
| Cable length          | 2 m                    |
| Core structure        | 3x AWG 18 + 16x AWG 22 |
| Total number of ports | 8                      |
| Number of contacts    | 5                      |

### Technical characteristics

|                                        |                    |
|----------------------------------------|--------------------|
| Rated current                          | 9 A                |
| Rated voltage                          | 10 V DC<br>30 V DC |
| Limiting temperature                   | -30 ... +85 °C     |
| Degree of protection acc. to IEC 60529 | IP67               |
| Number of channels per port            | 2                  |
| Circuit logic                          | PNP                |

### Material properties

|                  |           |
|------------------|-----------|
| Material (cable) | PVC       |
| RoHS             | compliant |
| ELV status       | compliant |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Yes           |
| California Proposition 65 substances | Nickel        |

## Specifications and approvals

|          |                                                 |
|----------|-------------------------------------------------|
| UL / CSA | UL 2238 CYJV.E500416<br>CSA-C22.2 CYJV7.E500416 |
|----------|-------------------------------------------------|

## Commercial data

|                                |                                                         |
|--------------------------------|---------------------------------------------------------|
| Packaging size                 | 1                                                       |
| Country of origin              | China                                                   |
| European customs tariff number | 85444290                                                |
| GTIN                           | 5713140277373                                           |
| eCl@ss                         | 27440108 Passive Sensor-Actuator-Interface (with cable) |
| ETIM                           | EC002585                                                |
| UNSPSC 24.0                    | 31251501                                                |