




Product designation
Product type designation


Description

Accessories for

Motor operator
P5X191D024UL
Motor operator
for remote
operation for UL
certified MCCBs..
Accessories for
UL-compliant
MCCBs

Operational characteristics		
Rated operational voltage	V	24VDC
Rated current (In)	A	≤2.5A
Mechanical operation	cycles/h	120
Average closing time	ms	350
Average opening time	ms	230
Power consumption	W	14
Mechanical features		
Weight	g	1300
Operations		
Mechanical life	cycles	25000
Dimensions		





Note: Connect an NC contact of an alarm switch contact block in series with S4 to prevent remote closing of the MCCB after tripping due to overcurrent or short circuit.

Wiring diagrams

Certifications and compliance

Certificates

cULus

ETIM classification

EC000066 - Power contactor, AC switching