

Crimpflange set



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 010 0022
Specification	Crimpflange set
HARTING eCatalogue	https://harting.com/21010100022

Identification

Category	Accessories
Series	Circular connectors M12
Identification	Slim Design
Type of accessory	Crimp flange set

Version

Details	HARTING offers to test and define the best crimp flange and ferrule combination for customer specific cables.
---------	---

Technical characteristics

Ambient temperature	-40 ... +85 °C
---------------------	----------------

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead



Pushing Performance
Since 1945

Material properties

Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	1
Net weight	7 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140236295
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400