

Datasheet

ECP4 Series

Constant Current LED Power Supply

ENGLISH



Features

- Input Voltage: 100 – 240Vac
- Input Frequency: 50/ 60Hz
- Output Power: 4W
- Fully encapsulated with IP66 rating
- Protections: Short circuit/ Overload/ Over Temp.
- Compact and light-weight plastic case
- 2 year warranty



Part number	Constant Current	Load	Max Output Voltage	PF	L x W x H
816-0153	350mA	1-4W	12VDC	≥0.4	38x 30x 23.5 mm
816-0157	500mA	1.5-4.5W	9.5VDC		
816-0166	700mA	1-4W	6VDC		

Mechanical Specification

- Safety According to EN61347-1, EN61347-2-13
- EMI According to EN55015
- EMS According to EN61000-3-2; EN61000-3-3; EN61547

Dimension in mm:

