

Dunlop Protomastor full safety (142YP)

Functional and multi-purpose work boot



General

Segment	Industry
Material boot shaft	PVC
Material outsole	PVC
Color boot shaft	Yellow
Color outsole	Black
Lining	White lining
Insole type	None

Certification

Safety standard Europe	EN ISO 20345:2011 S5 SRA
------------------------	--------------------------

Protection & Comfort

Toe cap	Steel
Midsole	Steel
Slip resistant outsole	SRA
Oil resistant outsole	Yes
Chemical resistant code	2
Energy absorbing	Yes
Electrical insulation	Antistatic
Fuel oil resistant	Yes

Sizing

Size range EUR	36-48
Size range UK	03-13

Logistics

Country of origin	PT
Intrastat code	64011000

USP's outsole

Oil resistant, SRA rated outsole for perfect grip

USP's shaft/upper

Waterproof to give protection in wet conditions

USP's safety

Slip resistant to assure safe working conditions

SKU	Size EUR	Size US	Size UK	GTIN	Prs/Outer pack	Outer pack length (mm)	Outer pack width (mm)	Outer pack height (mm)	Prs/Pallet	Pallet height (m)
142YP.36	36			8713197301271	6	385	385	268	216	
142YP.37	37		4	8713197301288	6	385	385	268	216	
142YP.38	38		5	8713197301295	6	385	385	355	180	
142YP.39	39		6	8713197301301	6	385	385	355	180	
142YP.40	40			8713197301318	6	385	385	355	180	
142YP.41	41		7	8713197301325	6	385	385	355	180	
142YP.42	42		8	8713197301332	6	385	385	355	180	
142YP.43	43		9	8713197301349	6	385	385	390	144	
142YP.44	44		10	8713197301356	6	385	385	390	144	
142YP.45	45			8713197301363	6	385	385	390	144	
142YP.46	46		11	8713197301370	6	385	385	425	144	
142YP.47	47		12	8713197301387	6	385	385	425	144	
142YP.48	48		13	8713197301394	6	385	385	425	144	

Creation date: April 24, 2020