

Product data sheet

179 N XXL-8 D/3

EAN-No. 4000896245178



3-pieces · 8 Drawers total



Application:

Efficient, mobile organisation of tools

- Tool trolley – extra deep
- 7 flat and 1 high drawer
- Complete with lateral door and socket strip (without assortment)

Work areas

- Much larger storage and work areas in stainless steel
- Fully sealed work surface protects inside of trolley from leaking liquids
- Interfaces integrated in the work area for accessories such as laptop holders and top modules
- Extra protection through high-quality plastic end caps

Body / Pull-handle

- Extremely robust design thanks to dual-wall structure
- Complete welded construction of the entire body for tough daily workshop use
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Ergonomically optimised pull handle for better manoeuvrability
- Brushed stainless steel handle

Locking concept

- Ergonomically arranged side lock position for better operability protects keys and lock against damage
- Highly secure closing system with central locking technology for optimum protection of your property
- 2-stage locking
 - Central locking, lockable with cylinder lock and 2 folding keys
 - Mutual drawer locking for minimum tilting risk

Drawer concept

- Self-closing and reciprocal locking of the drawers prevents unwanted opening
- 100% sliding-out with ball-bearing telescopic slides
- Drawer design for optimum use of the interior
- Drawer fronts for optimised handling
- Dirt-resistant drawer coating for easy cleaning

High performance chassis

Product data sheet

179 N XXL-8 D/3

EAN-No. 4000896245178



- Large wheels with high loading capacity, precision ball bearing and dual rounded rim in the pivot bearing, easy manoeuvrability, even with high dynamic load
- 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
- Protective ring prevents dirt and threads from getting in
- Elastic castors enable smooth movement
- Total loading capacity (dynamic): 750 kg
- Loading capacity (static): 1000 kg
- Loading capacity of high drawer: 40 kg
- Colour: HAZET blue
- Tool trolley Made in Germany
- Dimensions: 1167 mm x 642 mm x 1020 mm
- Net weight: 155.5 kg
- Drawers, flat: 7 x 81 x 870 x 522 mm
- Drawers, high: 1 x 166 x 870 x 522 mm
- (Drawer) size for plastic drawer insert: 1/2++ (2x)
- Worktop: Stainless steel
- Number of fixed castors: 2 (∅ 125 mm)
- Number of swivel castors: 2 (∅ 125 mm)
- Number of tools: 3

Order Number

179 N XXL-8 D/3



179NXXL-8D



161N-5D



179N-21D