

ENERGY AND AUTOMATION



Maxi Contactor Accesories



11G350 & 11G354 Aux Contact



11G355 Interlock



11G361 & 11G363 Pole Protection

Order code	Characteristics	
Auxiliary contacts. Faston terminals. Side mountinge.		
11 G350 ⊙	2NO+1NC or 1NO+2NC reversible	
11 G354 0	1NO+1NC	
Mechanical interlock.		
11 G355❷❸	Side by side	

Operational characteristics of auxiliary contacts

Type		G350-G354
IEC conventional free-air thermal current Ith	А	16
IEC rated insulation voltage Ui	V	690
Terminals Faston		1-6.35x0.8 2-2.8x0.8
Conductor section maximum (with 1 or 2 cables)		
flexible c/w lug	mm²	2.5
AWG	n°	14
UL/CSA and IEC/EN 60947-5-1	AC	A600
designation	DC	P600
Mechanical life (million)	cycles	5

Order code	Characteristics
Power terminal	protection.
11 G361®	For contactors B145-B180
11 G363®	For contactors B250-B310-B400

Provided for one pole terminal only. Example: For three-pole contactors, purchase 3 pieces for the upper terminals only or 6 pieces for all upper and lower terminals.