

8553

Thread cutting set

Code	ETIM
1939068	EC003884
EAN	UNSPSC
4010886869734	27-11-28-10
Country of origin	eCl@ss
European Union	21-01-02-09
Customs tariff number	
82055980	



Article description

- In plastic box
- Dimensions: 275 x 150 x 42 mm
- For internal thread M3 - M6
- For external threads M3 - M6, max. 40 mm long
- Ratchet drive system with extension unit
- Additional guide sleeve for dies to ensure accurately aligned thread cutting along the bar axis, with swarf collector
- Power tools:
- Ratchet with extension
- Tools for external threads:
- Die holder with guide discs and dies M3 - M6
- Die holder with guide discs and dies M3 - M6
- Quick acting chuck with tap M3 - M6
- Accessories:
- Fastening screws and angle screwdrivers

Article parts list

Cross handle ratchet 2093 U-3 T, Offset screwdriver 2 mm, Extension 1/4", Die holder, Clamping head tap holder, Grub screw M4x6, Washer, Guide disk M3 M4 M5 M6, Die M3 M4 M5 M6, Tap M3 M4 M5 M6

Article information

Contents (Qty of pieces)	1	Total height [mm]	42 mm
Net weight [kg]	0,51 kg	Storage	Plastic box
Total length [mm]	275 mm	appropriate for	Internal threads M3 - M6 and external threads M3 - M6, max. 40 mm long
Total width [mm]	150 mm		