



Main

Range of product	Multifix Air
Product or component type	Apparatus box
Device application	For airtight installation
Quantity per set	20 pieces

Complementary

Function available	Anti-rotation system
Number of gangs	2 gangs
Fixing mode	By supplied screw
Material	PP/TPE
Mechanical robustness	Fire resistance Airtight
Colour tint	Green NCS S 2070-G80Y
Cable entry	4 knock-outs
Distance between centers	71 mm
Drill diameter/depth	67 mm 40 mm
Height	71 mm
Width	142 mm
Depth	39 mm

Environment

Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP20
Fire resistance	850 °C
Standards	EN 60670-1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0852 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------