



ENGLISH

Datasheet

Stock No: 273-107

# RS Pro Manual Die Cast Aluminium 2.6kW Hand Dryer, 177mm x 264mm x 275mm



## Product Details

### Heavy Duty Hand and Face Dryers

High quality, manual or automatic hand/face dryers designed for use in aggressive environments.

Vandal resistant, pressure die cast aluminium case with an epoxy/polyester powder coat

Maximum temperature 60°C

20mm rear and bottom conduit entry

Template with comprehensive instructions

## Specifications:

|                  |                    |
|------------------|--------------------|
| Air Flow         | 275m³/h            |
| Case Material    | Die Cast Aluminium |
| Supply Voltage   | 220 → 240V ac      |
| Automatic/Manual | Manual             |
| Power Rating     | 2.6kW              |
| Depth            | 177mm              |
| Height           | 264mm              |
| Width            | 275mm              |