



Body protection

SOCCIAHV Fluorescent yellow-Black

OUTDOOR HIGH VISIBILITY

Class 2 HV softshell, removable sleeves, segmented bands for good visibility in dangerous or low light environments



Specific benefits



Comfort

- 4-way stretch for total freedom of movement
- 2-layer complex for added lightness



Performance

- Water-repellent fabric to keep you dry in light rain



Ease of use

- 2 in 1 garment to adapt to changing temperatures



Durability

- Certified EN ISO 20471 after 25 washes



Easy to use

Technologies & labels



STRETCH 4 DIRECTIONS

- Segmented strip



100% recycled polyester

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Transportation

Certifications and norms



EN ISO 13688

Protects against risks



High vis



Weather



Body protection

SOCCIAHV Fluorescent yellow-Black

OUTDOOR HIGH VISIBILITY

Class 2 HV softshell, removable sleeves, segmented bands for good visibility in dangerous or low light environments

Standards - Details

Technical details

Collection	All year round
Type of workwear	2 in 1 water-repellent softshell
Gender	Mixte
Size range	S → 3XL
Workwear color	Black, Yellow
Support material details	Softshell - 96% recycled polyester 4% recycled elastane - two-rolled-layers
Total product weight (g/m ²)	280
Fastening	Zipper fastening
Sleeve size	Removable sleeves
Lower sleeve	Bias
Lower body	Bottom drawstring
Top Reflective piping	Chest (2 bands)
Number of exterior pockets	4
External pockets	4 zipped pockets
Number of inside pockets	2
Inner pockets	2 inner pockets
Marking type	Embroidery, Screen printing, Transfer printing
Laminated lining material	Polyester polar fleece 280 g/m ²
Modularity options	Jacket with sleeves, Sleeveless jacket
Reflective segmented tapes	yes








SOCCIAHV

OUTDOOR HIGH VISIBILITY

Protective clothing

Class 2 HV softshell, removable sleeves, segmented bands for good visibility in dangerous or low light environments

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
SOCCSOH201FO KSM [SOCHVORPT]	Fluorescent orange-Black	S	SOCCIAHV	3295249311421	13295249311428	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FO KMD [SOCHVORTM]	Fluorescent orange-Black	M	SOCCIAHV	3295249311483	13295249311480	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FO KLG [SOCHVORGT]	Fluorescent orange-Black	L	SOCCIAHV	3295249311490	13295249311497	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FO KXL [SOCHVORXG]	Fluorescent orange-Black	XL	SOCCIAHV	3295249311506	13295249311503	10	1	8.2 kg	60.0 cm	41.0 cm	34.0 cm
SOCCSOH201FO K2X [SOCHVORXX]	Fluorescent orange-Black	XXL	SOCCIAHV	3295249311513	13295249311510	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FO K3X [SOCHVOR3X]	Fluorescent orange-Black	3XL	SOCCIAHV	3295249311520	13295249311527	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FY KSM [SOCHVJAPT]	Fluorescent yellow-Black	S	SOCCIAHV	3295249311414	13295249311411	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FY KMD [SOCHVJATM]	Fluorescent yellow-Black	M	SOCCIAHV	3295249311438	13295249311435	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FY KLG [SOCHVJAGT]	Fluorescent yellow-Black	L	SOCCIAHV	3295249311445	13295249311442	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FY KXL [SOCHVJAXG]	Fluorescent yellow-Black	XL	SOCCIAHV	3295249311452	13295249311459	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FY K2X [SOCHVJAXX]	Fluorescent yellow-Black	XXL	SOCCIAHV	3295249311469	13295249311466	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm
SOCCSOH201FY K3X [SOCHVJA3X]	Fluorescent yellow-Black	3XL	SOCCIAHV	3295249311476	13295249311473	10	1	8.2 kg	60.0 cm	41.0 cm	24.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height