

Parker Product Datasheet



PXV-series visual indicators give an immediate and clear information about pressure actuation. Available in Ø22mm and Ø30mm sizes, with a large choice of colours.

PART NUMBER: PXV-F111

COLOR: White (actuated) / Black (unactuated)

PRODUCT OVERVIEW

Pneumatic visual indicators give an immediate and clear information about pressure actuation. They exist in Ø22mm and Ø30mm with a large choice of colours.

Markets

- Factory Automation
- Miscellaneous Industrial
- Miscellaneous Manufacturing

Features/Benefits

- Lightning fast response
- Simple long life mechanism
- Very high contrast
- All around visibility
- One single pipe connection
- Effective aid to diagnostics

Applications

- Man/machine dialogue
- Cabinet visualisation

TECH SPECIFICATIONS

DIVISION	Electric Motion and Pneumatic Division - Europe
SPECIFICATIONS MET	-
PRODUCT TYPE	Visual Indicators
OPERATING TEMPERATURE	-15° to +60° °C
MAXIMUM FLOW RATE	-
PRESSURE RATING	1 to 8 bar