



10125012

1in x 17.02 mm - Chain sprockets ISO

2D Technical Drawing



Dynamic 3D View



Technical Specifications

Number of teeth (T)	12
de (DE) mm	109.26
dp (DP) mm	98.14
Part number (CODE)	10125012
dm (DM) mm	69
D1 (D1) mm	16
A (A) mm	40
Tooth radius r3 (R3) mm	26
Radius width C (C) mm	2.5
Sprockets tooth width B1 (B1) mm	16.2
Weight (WEIGHT) kg	1.43
Material (MAT)	STEEL C 45