

Technical data sheet

Article number:
924-00417

LBD5W

Product Group	Lip Blade Terminals
Product Family	Double Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Yellow (YE)
Application Range	Low Voltage
Conductor Size Range mm ²	4.0-6.0 mm ²
Diameter (D)	6.8 mm
Length (L)	31.8 mm
Length (L2)	14 mm
Length (L3)	17.3 mm
Max Current	48 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	4.6 mm
Width (W3)	3 mm

RoHS 