



PRODUCT DATASHEET

Datasheet creation date: 2025/07/09 8:02 (UTC)



6305DDU

Single-Row Deep Groove Ball Bearings

Parts Number

6305DDUC3

Boundary Dimensions

d	25	mm	Bore diameter
D	62	mm	Outside diameter
B	17	mm	Width
r (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	22600	N	Basic dynamic load rating
C0r	11200	N	Basic static load rating

Speeds

Grease	8000	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	31.5	mm	Diameter of shaft abutment
da (max.)	36	mm	Diameter of shaft abutment
Da (max.)	55.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	13.2	Factor
----	------	--------

Additional information

z	8	Number of Balls
Dw	10.319	mm Ball Diameter

Mass

Mass approx.	0.235	kg	Mass approx.
--------------	-------	----	--------------

