

Datasheet

RS Pro 1 Way Connection & Termination Block, Screw Down, 450 V, Clear

RS Stock No: **315-6308**



Product Details

RS Pro 2-way earth block in green/yellow colour, has a nylon housing construction for longer life. This earth block has high current fingerproof screwdown terminals for easy termination. The earth block supports 8 to 20 AWG cables of 6 to 35 mm² CSA. It is current rated for 41 A and voltage rated for 800 V. It measures 54 x 8 x 61.5 mm.

Features and Benefits

- Fingerproof terminals (to VBG4 requirements)
- Flammability rating UL94V-0
- Cable sizes from 6 - 35 mm²
- Mounting method DIN rail (top hat rail)/G-rail



ENGLISH

Specifications:

Cable CSA	25 mm ²
Colour	Clear
Height	43.5 mm
Length	20.8 mm
Maximum Operating Temperature	+85°C
Number of Ways	1
Termination Method	Screw Down
Voltage Rating	450 V
Width	42.5 mm
Wire Size	3 AWG