



## NEMIQ 50

E1630210

Crimping Tool Multi, Insulated KD, KR & Non-Insulated KD.

### Product Properties:

Number of crimps	1
With locking device (for mechanical tools)	No
Inserts exchangeable	No
With automatic return	No
Suitable for	Cable lugs and connectors
Construction/operation	Mechanical
Compression shape	Oval pressing

### Dimensions:

Cross section	0.5-6 mm <sup>2</sup>
MOQ	1 .
Unit	pcs
Length	230 mm

### Approvals:

### Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	In compliance
PFAS	No PFAS
REACH	No SVHC (250 Subs. 25 June 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
ECCN (EU)	No CLASS

ECCN (US)

EAR99

### **Other information:**

<b>ETIM-Class</b>	EC000168 - Crimp tool cable lugs, cable end sleeves, screen connection
<b>ETIM-Release</b>	10.0
<b>Trademark</b>	NEMIQ
<b>Product Group</b>	One Hand
<b>Search Description</b>	NELCO 50
<b>Alternative SKU</b>	NEMIQ50
<b>E-no</b>	E1630210

### **Logistic information:**

<b>Barcode</b>	733117631711
<b>Country of origin</b>	TW
<b>E-no</b>	E1630210
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	1 .
<b>Stock code</b>	NEMIQ 50
<b>Taric code</b>	82032000
<b>Unit</b>	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.