



NEU
NEW



Product information

LED Light JARO 3000 2930lm, 30W, IP65

For interior and exterior wall mounting, IP 65.

- LED Light with extra bright Everlight SMD LEDs.
- User-friendly mounting with external waterproof connection terminal (10 - 50 W) or connection box (80 - 100 W).
- With safety glass.
- Solid and modern aluminium casing.
- Adjustable mounting bracket for mounting.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.

Technical information

Product number	1171250331
EAN-Code	4007123656301
UP	1
Total luminous flux	2930 lm
Power	30 W
Colour temperature	6500 K
Efficacy	95 lm/W
Energy efficiency class	A+
Nominal input voltage	230 V
Max. nominal input voltage	240 V
Degree of protection (IP)	IP65
Protection class	I
Colour	silver
fittings	Without
Weight of product (without packaging)	1.16 kg
Length of product (without packaging)	22.90 cm
Width of product (without packaging)	7.25 cm
Height of product (without packaging)	25.50 cm
Weight of product (including packaging)	1.32 kg



Length of product (including packaging)	25.50 cm
Width of product (including packaging)	7.50 cm
Height of product (including packaging)	18.50 cm