

Han-Brid Quintax M snap-fit



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 003 3002
Specification	Han-Brid Quintax M snap-fit
HARTING eCatalogue	https://harting.com/09150033002

Identification

Category	Inserts
Series	Han-Brid®
Identification	Han-Brid® Quintax 3 A
Specification	Snap-in latches snap-fit

Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	1
	4
	8
further contacts	+ shielding + 2 power contacts
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140186644
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522