



Hauptmerkmale

Produkt oder Komponententyp	Motordrossel
Kompatible Produktfamilie	Altivar 61 Altivar 71 Altivar 212 Altivar 61Q Altivar 71Q Altivar Process ATV600 Altivar Process ATV900
Produktspezifische Anwendung	Ausgangsfilter
Nennstrom [In]	215 A
Produktkompatibilität	ATV212HU15N4 ATV212HD15M3X ATV71WU55N4 ATV71WU75N4 ATV71PD11N4Z ATV71WD11N4 ATV71WD15N4 ATV71WD18N4 ATV71WD30N4 ATV71WD37N4 ATV71WD45N4 ATV71WD55N4 ATV71WD75N4 ATV61QC11N4 ATV71QD90N4 ATV61WD11N4 ATV61WD11N4C ATV61WD15N4 ATV61WD15N4C ATV61WD18N4 ATV61WD18N4C ATV61WU55N4 ATV61WU55N4C ATV61WU75N4 ATV61WU75N4C ATV61WD22N4 ATV61WD22N4C ATV61WD30N4 ATV61WD30N4C ATV61WD37N4 ATV61WD37N4C ATV212WD15N4 ATV212WD15N4C

ATV61QC13Y
ATV61WD45N4
ATV61WD45N4C
ATV61WD55N4
ATV61WD55N4C
ATV61WD75N4
ATV61WD75N4C
ATV61WD90N4
ATV61WD90N4C
ATV71QC11Y
Variable speed drive ATV630 motor: 2.2 kW 500...690 V three phase
Variable speed drive ATV630 motor: 3 kW 500...690 V three phase
Variable speed drive ATV630 motor: 4 kW 500...690 V three phase
Variable speed drive ATV630 motor: 5.5 kW 500...690 V three phase
Variable speed drive ATV630 motor: 7.5 kW 500...690 V three phase
Variable speed drive ATV630 motor: 11 kW 500...690 V three phase
Variable speed drive ATV930 motor: 2.2 kW 500...690 V three phase
Variable speed drive ATV930 motor: 3 kW 500...690 V three phase
Variable speed drive ATV930 motor: 4 kW 500...690 V three phase
Variable speed drive ATV930 motor: 5.5 kW 500...690 V three phase
Variable speed drive ATV930 motor: 7.5 kW 500...690 V three phase
Variable speed drive ATV930 motor: 11 kW 500...690 V three phase
Variable speed drive ATV630 600 V, 3 hp three phase
Variable speed drive ATV630 600 V, 5 hp three phase
Variable speed drive ATV630 600 V, 7.5 hp three phase
Variable speed drive ATV630 600 V, 10 hp three phase
Variable speed drive ATV630 600 V, 15 hp three phase
Variable speed drive ATV930 600 V, 3 hp three phase
Variable speed drive ATV930 600 V, 5 hp three phase
Variable speed drive ATV930 600 V, 7.5 hp three phase
Variable speed drive ATV930 600 V, 10 hp three phase
Variable speed drive ATV930 600 V, 15 hp three phase
Variable speed drive ATV630 motor: 15 kW 500...690 V three phase
Variable speed drive ATV630 motor: 18.5 kW 500...690 V three phase
Variable speed drive ATV630 motor: 22 kW 500...690 V three phase
Variable speed drive ATV630 motor: 30 kW 500...690 V three phase
Variable speed drive ATV630 motor: 37 kW 500...690 V three phase
Variable speed drive ATV630 motor: 45 kW 500...690 V three phase
Variable speed drive ATV630 motor: 55 kW 500...690 V three phase
Variable speed drive ATV630 motor: 75 kW 500...690 V three phase
Variable speed drive ATV630 motor: 90 kW 500...690 V three phase
Variable speed drive ATV930 motor: 15 kW 500...690 V three phase
Variable speed drive ATV930 motor: 18.5 kW 500...690 V three phase
Variable speed drive ATV930 motor: 22 kW 500...690 V three phase
Variable speed drive ATV930 motor: 30 kW 500...690 V three phase
Variable speed drive ATV930 motor: 37 kW 500...690 V three phase
Variable speed drive ATV930 motor: 45 kW 500...690 V three phase
Variable speed drive ATV930 motor: 55 kW 500...690 V three phase
Variable speed drive ATV930 motor: 75 kW 500...690 V three phase
Variable speed drive ATV930 motor: 90 kW 500...690 V three phase
Variable speed drive ATV630 600 V, 20 hp three phase
Variable speed drive ATV630 600 V, 25 hp three phase
Variable speed drive ATV630 600 V, 30 hp three phase
Variable speed drive ATV630 600 V, 40 hp three phase
Variable speed drive ATV630 600 V, 50 hp three phase
Variable speed drive ATV630 600 V, 60 hp three phase
Variable speed drive ATV630 600 V, 75 hp three phase
Variable speed drive ATV630 600 V, 100 hp three phase
Variable speed drive ATV930 600 V, 20 hp three phase
Variable speed drive ATV930 600 V, 25 hp three phase
Variable speed drive ATV930 600 V, 30 hp three phase
Variable speed drive ATV930 600 V, 40 hp three phase
Variable speed drive ATV930 600 V, 50 hp three phase
Variable speed drive ATV930 600 V, 60 hp three phase
Variable speed drive ATV930 600 V, 75 hp three phase
Variable speed drive ATV930 600 V, 100 hp three phase
ATV61HC11Y
ATV61HC13Y
ATV61HC16Y
ATV61HD11N4
ATV61HD15N4
ATV61HD15Y
ATV61HD18N4
ATV61HD18Y
ATV61HD22N4
ATV61HD22Y

ATV61HD30M3X
 ATV61HD30N4
 ATV61HD30Y
 ATV61HD37M3X
 ATV61HD37N4
 ATV61HD37Y
 ATV61HD45M3X
 ATV61HD45N4
 ATV61HD45Y
 ATV61HD55N4
 ATV61HD55Y
 ATV61HD75N4
 ATV61HD75Y
 ATV61HD90N4
 ATV61HD90Y
 ATV61HU55N4
 ATV61HU75N4
 ATV71HC11Y
 ATV71HC13Y
 ATV71HD11N4
 ATV71HD11Y
 ATV71HD15N4
 ATV71HD15Y
 ATV71HD18N4
 ATV71HD18Y
 ATV71HD22N4
 ATV71HD22Y
 ATV71HD30M3X
 ATV71HD30Y
 ATV71HD37M3X
 ATV71HD37N4
 ATV71HD37Y
 ATV71HD45M3X
 ATV71HD45N4
 ATV71HD45Y
 ATV71HD55N4
 ATV71HD55Y
 ATV71HD75N4
 ATV71HD75Y
 ATV71HD90N4
 ATV71HD90Y
 ATV71HU55N4
 ATV71HU75N4
 ATV71PU55N4Z
 ATV71PU75N4Z
 ATV61HU22S6X
 ATV61HU30S6X
 ATV61HU40S6X
 ATV61HU55S6X
 ATV61HU75S6X
 ATV71HU15S6X
 ATV71HU22S6X
 ATV71HU30S6X
 ATV71HU40S6X
 ATV71HU55S6X
 ATV71HU75S6X

Benötigte Menge	3
Elektrische Verbindung	Etikett Stecker M10

Zusatzmerkmale

Motorkabellänge <= 150 m abgeschirmtes Kabel P Motor 30-45 kW bei 200...240 V 1 <= 300 m ungeschirmtes Kabel P Motor 30-45 kW bei 200...240 V 1 <= 200 m abgeschirmtes Kabel P Motor 5,5-18,5 kW bei 380...480 V 1 <= 300 m ungeschirmtes Kabel P Motor 5,5-18,5 kW bei 380...480 V 1 <= 150 m abgeschirmtes Kabel P Motor 22-30 kW bei 380...480 V 1 <= 300 m ungeschirmtes Kabel P Motor 22-30 kW bei 380...480 V 1 <= 150 m abgeschirmtes Kabel P Motor 45-75 kW bei 380...480 V 1 <= 300 m ungeschirmtes Kabel P Motor 45-75 kW bei 380...480 V 1 <= 150 m abgeschirmtes Kabel P Motor 2,2-7,5 kW bei 500-600 V 1 <= 250 m ungeschirmtes Kabel P Motor 2,2-7,5 kW bei 500-600 V 1 <= 250 m abgeschirmtes Kabel P Motor 2,2-7,5 kW bei 500-600 V 2 <= 400 m ungeschirmtes Kabel P Motor 2,2-7,5 kW bei 500-600 V 2 <= 100 m abgeschirmtes Kabel P Motor 2,2-30 kW bei 500...690 V 1

<= 150 m ungeschirmtes Kabel P Motor 2,2-30 kW bei 500...690 V 1
 <= 150 m abgeschirmtes Kabel P Motor 11-30 kW bei 500...690 V 2
 <= 250 m ungeschirmtes Kabel P Motor 11-30 kW bei 500...690 V 2
 <= 150 m abgeschirmtes Kabel P Motor 30-160 kW bei 500...690 V 1
 <= 250 m ungeschirmtes Kabel P Motor 30-160 kW bei 500...690 V 1
 <= 250 m abgeschirmtes Kabel P Motor 30-160 kW bei 500...690 V 2
 <= 300 m ungeschirmtes Kabel P Motor 30-90 kW bei 500...690 V 2
 <= 400 m ungeschirmtes Kabel P Motor 90-160 kW bei 500...690 V 2
 <= 200 m abgeschirmtes Kabel P Motor 37 kW bei 380...480 V 1
 <= 300 m ungeschirmtes Kabel P Motor 37 kW bei 380...480 V 1
 <= 200 m abgeschirmtes Kabel P Motor 90 kW bei 380...480 V 1
 <= 300 m ungeschirmtes Kabel P Motor 90 kW bei 380...480 V 1

Dv/Dt	500 V/μs max. bei 400 V 750 V/μs max. bei 500 V 1000 V/μs max. bei 690 V
Thermische Verluste	430 W
Max. Ausgangsfrequenz des Frequenzumrichters	100 Hz
Umgebungstemperatur bei Betrieb	-10-50 °C
Produktgewicht	15.5 kg

Montage

Schutzart (IP)	IP20 (with kits VW3A9612,613) IP00
Umgebungstemperatur bei Lagerung	-25 -70 °C

Vertragliche Gewährleistung

Periode	18 Monate
---------	-----------