

Camglass GP



Advantages

- Robust construction
- Comprehensive range of standard and non standard sizes
- Moisture resistant cardboard frame
- Gradual density media to improve dust holding capacity

Application: Pre filter for comfort air conditioning applications.

Type: Disposable panel filter.

Case: Moisture resistant cardboard.

Media: Glass fibre.

EN 779:2012 efficiency: G2, G3.

Gravimetric efficiency: 75% - 85%.

Eurovent 4/5 efficiency: EU2, EU3.

Recommended final pressure drop: 250 Pa.

Temperature: 70°C maximum in continuous service.

Holding frames: Front and side access housings and frames are available, Type 8, Type L, and FC Housings.

Reference	Type	Model	Dimensions (WxHxD) mm	Filter classification EN779:2012	Media area m ²	Air flow / pressure drop m ³ /hr/Pa	Unit volume m ³	Unit weight kg
GP12242NOM	Camglass GP	GP12242NOM	305x610x50	G3	0.19	1200/50	0.01	0.20
GP15152NOM	Camglass GP	GP15152NOM	381x381x50	G3	0.15	990/50	0.01	0.15
GP15202NOM	Camglass GP	GP15202NOM	381x508x50	G3	0.19	1315/50	0.01	0.20
GP16202NOM	Camglass GP	GP16202NOM	406x508x50	G3	0.21	1400/50	0.01	0.20
GP16252NOM	Camglass GP	GP16252NOM	406x635x50	G3	0.26	1750/50	0.02	0.25
GP18182NOM	Camglass GP	GP18182NOM	457x457x50	G3	0.21	1400/50	0.02	0.20
GP20202NOM	Camglass GP	GP20202NOM	508x508x50	G3	0.26	1750/50	0.02	0.25
GP20242NOM	Camglass GP	GP20242NOM	508x610x50	G3	0.31	1460/50	0.02	0.30
GP20252NOM	Camglass GP	GP20252NOM	508x635x50	G3	0.32	2100/50	0.02	0.35
GP24242NOM	Camglass GP	GP24242NOM	610x610x50	G3	0.37	2400/50	0.02	0.40
GP12241NOM	Camglass GP	GP12241NOM	305x610x25	G2	0.19	1200/45	0.01	0.20
GP15151NOM	Camglass GP	GP15151NOM	381x381x25	G2	0.15	990/45	0.01	0.15
GP15201NOM	Camglass GP	GP15201NOM	381x508x25	G2	0.19	1315/45	0.01	0.20
GP16201NOM	Camglass GP	GP16201NOM	406x508x25	G2	0.21	1400/45	0.01	0.20
GP16251NOM	Camglass GP	GP16251NOM	406x635x25	G2	0.26	1750/45	0.01	0.25
GP18181NOM	Camglass GP	GP18181NOM	457x457x25	G2	0.21	1400/45	0.01	0.20
GP20201NOM	Camglass GP	GP20201NOM	508x508x25	G2	0.26	1750/45	0.01	0.25
GP20241NOM	Camglass GP	GP20241NOM	508x610x25	G2	0.31	1460/45	0.01	0.30
GP20251NOM	Camglass GP	GP20251NOM	508x635x25	G2	0.32	2100/45	0.01	0.35
GP24241NOM	Camglass GP	GP24241NOM	610x610x25	G2	0.37	2400/45	0.01	0.40

Other sizes are available on request. All dimensions are nominal.